

# Cable to Web of Rail Complete Welder, Power



## **FEATURES**

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

## **SPECIFICATIONS**

Material: Graphite;Steel;Thermoplastic

**Bond Terminal Style:** W

Table 1/1								
Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation			
PBWY301RH	UIC60	50 mm <sup>2</sup> Concentric	0.35"	T20	Right Hand			
PBWT202JRH	85 lb to 141 lb T- Rail Sections	2/0 Ropelay	0.48"	T20	Right Hand			
PBWT202JLH	85 lb to 141 lb T- Rail Sections	2/0 Ropelay	0.48"	T20	Left Hand			
PBWT20X5RH	85 lb to 141 lb T- Rail Sections	95 mm² Ropelay	0.61"	T20	Right Hand			
PBWT20X5LH	85 lb to 141 lb T- Rail Sections	95 mm² Ropelay	0.61"	T20	Left Hand			
PBWT202WLH	85 lb to 141 lb T- Rail Sections	250 kcmil Ropelay	3/4"	T20	Left Hand			

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBWT202WRH	85 lb to 141 lb T- Rail Sections	250 kcmil Ropelay	3/4"	T20	Right Hand
PBWT203SLH	85 lb to 141 lb T- Rail Sections	500 kcmil Ropelay	1.04"	T20	Left Hand
PBWT203SRH	85 lb to 141 lb T- Rail Sections	500 kcmil Ropelay	1.04"	T20	Right Hand

### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

MARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

# North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

### **APAC**

Shanghai: + 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE