

Cable to Web of Rail Mold Only, Power



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

Connections for power or grounding conductor to the neutral axis

SPECIFICATIONS

Material: Graphite

Bond Terminal Style: W

Table 1/1

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBWH2LH	85 lb to 141 lb T-Rail Sections	35 mm ² Concentric	0.3"	T20	Left Hand
PBWH2RH	85 lb to 141 lb T-Rail Sections	35 mm ² Concentric	0.3"	T20	Right Hand
PBWX3RH	85 lb to 141 lb T-Rail Sections	50 mm ² Ropelay	0.36"	T20	Right Hand
PBW2CLH	85 lb to 141 lb T-Rail Sections	1/0 Concentric	0.37"	T20	Left Hand
PBW2CRH	85 lb to 141 lb T-Rail Sections	1/0 Concentric	0.37"	T20	Right Hand
PBW2GLH	85 lb to 141 lb T-Rail Sections	2/0 Concentric	0.42"	T20	Left Hand

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBW2GRH	85 lb to 141 lb T-Rail Sections	2/0 Concentric	0.42"	T20	Right Hand
PBW2JLH	85 lb to 141 lb T-Rail Sections	2/0 Ropelay	0.48"	T20	Left Hand
PBW2JRH	85 lb to 141 lb T-Rail Sections	2/0 Ropelay	0.48"	T20	Right Hand
PBW2QLH	85 lb to 141 lb T-Rail Sections	4/0 Concentric	0.53"	T20	Left Hand
PBW2QRH	85 lb to 141 lb T-Rail Sections	4/0 Concentric	0.53"	T20	Right Hand
PBWS6LH	85 lb to 141 lb T-Rail Sections	3/0 Composite	0.57"	T20	Left Hand
PBWS6RH	85 lb to 141 lb T-Rail Sections	3/0 Composite	0.57"	T20	Right Hand
PBW2SLH	85 lb to 141 lb T-Rail Sections	4/0 Ropelay	0.61"	T20	Left Hand
PBW2SRH	85 lb to 141 lb T-Rail Sections	4/0 Ropelay	0.61"	T20	Right Hand
PBWX5LH	85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	0.61"	T20	Left Hand
PBWX5RH	85 lb to 141 lb T-Rail Sections	95 mm ² Ropelay	0.61"	T20	Right Hand
PBWX7LH	85 lb to 141 lb T-Rail Sections	150 mm ² Ropelay	0.67"	T20	Left Hand
PBWX7RH	85 lb to 141 lb T-Rail Sections	150 mm ² Ropelay	0.67"	T20	Right Hand
PBW2W010LH	R13, RI52	250 kcmil Ropelay	3/4"	T20	Left Hand
PBW2W010RH	R13, RI52	250 kcmil Ropelay	3/4"	T20	Right Hand
PBW2WLH	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	3/4"	T20	Left Hand
PBW2WLK1LH	LK1 Girder Rail	250 kcmil Ropelay	3/4"	T20	Left Hand
PBW2WLK1RH	LK1 Girder Rail	250 kcmil Ropelay	3/4"	T20	Right Hand

Catalog Number	Rail Type	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation
PBW2WRH	85 lb to 141 lb T-Rail Sections	250 kcmil Ropelay	3/4"	T20	Right Hand
PBWX8LH	85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	0.8"	T20	Left Hand
PBWX8RH	85 lb to 141 lb T-Rail Sections	185 mm ² Ropelay	0.8"	T20	Right Hand
PBW3FRH	85 lb to 141 lb T-Rail Sections	350 kcmil Ropelay	0.88"	T20	Right Hand
PBWX902LH	85 lb to 141 lb T-Rail Sections	240 mm ² Ropelay	0.93"	T20	Left Hand
PBWX902RH	85 lb to 141 lb T-Rail Sections	240 mm ² Ropelay	0.93"	T20	Right Hand
PBW3S002LH	RI60	500 kcmil Ropelay	1.04"	T20	Left Hand
PBW3S002RH	RI60	500 kcmil Ropelay	1.04"	T20	Right Hand
PBW3SLH	85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	1.04"	T20	Left Hand
PBW3SLK1LH	LK1 Girder Rail	500 kcmil Ropelay	1.04"	T20	Left Hand
PBW3SLK1RH	LK1 Girder Rail	500 kcmil Ropelay	1.04"	T20	Right Hand
PBW3SRH	85 lb to 141 lb T-Rail Sections	500 kcmil Ropelay	1.04"	T20	Right Hand

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE