

Closed Circuit Television Protector



FEATURES

Robust high energy protection

Compact package for limited space requirements


Isolated ground prevents introduction of unwanted noise

SPECIFICATIONS

Catalog Number	CCTV12
Nominal System Voltage (Un)	+/- 12 VDC
Max Continuous Operating Voltage (Uc)	+/- 14 VDC
Voltage Protection Level (Up)	60 V @ 5 kA
Nominal Discharge Current (In)	10kA 8/20 μ s
Frequency	100 Hz Max
Transmission Rate	16Mbit/s
Impedance	50 - 75 Ω
Connection Type	BNC, Female
Mounting	In-line insertion
Temperature	-13 to 158 °F
Enclosure Material	Metal
Enclosure Rating	IP 20 NEMA®-1
Depth (D)	1.1"

Catalog Number	CCTV12
Height (H)	3.54"
Width (W)	0.87"
Unit Weight	2.12 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE