

Conductor Sleeve



FEATURES

Used to adapt a limited range of smaller size cables to a larger size nVent ERICO Cadweld Mold

Provides strength and stability on finely-stranded copper conductors

SPECIFICATIONS

Material: Copper

Table 1/1

Catalog Number	Finish	Type	Length (L)	Thickness (T)	Diameter (Ø)
S429F2J16	Tinned	Flared	1"	0.02"	0.48"
S429F2N16	Tinned	Flared	1"	0.02"	0.54"
B112	Tinned	Straight	1.06"	0.03"	0.21"
B1331K	Tinned	Straight	1"	0.03"	0.14"
PBS24F	Tinned	Flared	1 1/2"	0.03"	0.8"
S02F	Tinned	Flared	1"	0.03"	0.61"
S03F	Tinned	Flared	1"	0.03"	0.46"

Catalog Number	Finish	Type	Length (L)	Thickness (T)	Diameter (Ø)
S05F	Tinned	Flared	1"	0.03"	0.39"
S07F	Tinned	Flared	1"	0.03"	0.67"
S17F	Tinned	Flared	1"	0.03"	0.34"
S429F3S20	Tinned	Flared	1 1/4"	0.03"	0.93"
H101		Straight	1.02"	0.04"	0.24"
H102		Straight	0.98"	0.04"	0.17"
H102F		Flared	1.02"	0.04"	0.17"
H105		Straight	0.93"	0.04"	0.12"
H106AF		Flared	1.38"	0.04"	0.59"
H106F		Flared	1.02"	0.04"	0.59"
H113F		Flared	1.02"	0.04"	0.31"
H117		Straight	0.98"	0.04"	0.28"
H103		Straight	0.98"	0.05"	0.21"
180380	Tinned	Flared	0.98"	0.09"	0.21"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE