

Copper Utility Ground Plate



The Copper Utility Ground Plate is designed to create an equipotential plane and help protect personnel and valuable equipment. This is particularly important in the utility industry, where safety is a top priority. The plate's large surface area helps to dissipate current into the ground, reducing the risk of electrical shock and equipment damage. Additionally, the plate is available with a pigtail configuration, making it a versatile solution for various applications within the irrigation industry.

FEATURES

Provides a large surface area to dissipate current into the ground

Lays flat underground and can attach the pigtail via a ground rod


SPECIFICATIONS

Table 1/1

Catalog Number	Material	Connector	Length (L)	Width (W)	Thickness (T)
UGP496	Copper		96"	4	0.06
UGP436	Copper		36"	4	0.06
UGP738		SRGC46	38 1/2"	7 1/2"	1/16"
UGP719SBP5		ESB2 Split Bolt	19 1/4"	7 1/2"	1/16"
UGP738P10		SRGC46	38 1/2"	7 1/2"	1/16"
UGP719		SRGC46	19 1/4"	7 1/2"	1/16"
UGP738P5		SRGC46	38 1/2"	7 1/2"	1/16"
UGP719BP5		SRGC46	19 1/4"	7 1/2"	1/16"

Catalog Number	Material	Connector	Length (L)	Width (W)	Thickness (T)
UGP738SBP5		ESB2 Split Bolt	38 1/2"	7 1/2"	1/16"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE