

Copper Utility Ground Plate, One Pigtail





The nVent ERICO Copper Utility Ground Plate with One Pigtail is a grounding and bonding solution designed for the Irrigation industry. The pigtail is welded using a Cadweld exothermic connection to create a permanent molecular bond that will not loosen or corrode, ensuring the durability and reliability of the system. The ground plate provides a large surface area to dissipate current into the ground, which is beneficial in areas with high resistivity, such as rocky, sandy, or shallow soil conditions, where using only a ground rod may not be feasible. The pigtail provides added flexibility in the placement of the ground plate.

FEATURES

Provides a large surface area to dissipate current into the ground

Available in a variety of sizes and pigtail configurations

SPECIFICATIONS

Material: Copper

Table 1/1									
Catalog Number	Length 1 (L1)	Length 2 (L2)	Width (W)	Thickness (T)	Conductor Size	Insulated			
UGP496GW6F2 5	96"	300"	4"	0.06"	#6 Solid	Yes			
UGP4966F25	96"	300"	4"	0.06"	#6 Solid	No			
UGP436GW10F 15	36"	180"	4"	0.06"	#10 Solid	Yes			

CatalogNumber	Length 1 (L1)	Length 2 (L2)	Width (W)	Thickness (T)	Conductor Size	Insulated
UGP436GW6F2 5	36"	300"	4"	0.06"	#6 Solid	Yes

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE