

Special Track Work Mold Only, Signal, 1" Tab Bond Terminal Style, Manganese Frog

CATALOG NUMBER

SBB343E



CERTIFICATIONS



FEATURES

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

PRODUCT ATTRIBUTES

Material: Graphite

Bond Terminal Style: 1" Tab

Rail Type: Manganese Frog

Conductor Size: 3/16" Bondstrand

Conductor Outer Diameter, Nominal: 0.19"

Welder Style: TB4

Mold Only: Yes

Welding Material: SB32, Sold Separately

Handle Clamp: B323W, Sold Separately

Bond Clip: B3388, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE