

Industrial Stack Base with Stud, Horizontal/Vertical Cable Run



FEATURES

Cast air terminal base for use with horizontal and/or vertical conductor runs

Welded threaded stud for use with expansion anchors

SPECIFICATIONS

Material: Bronze

Conductor Size, UL: Class 2 (4/0 Max)

Table 1/2

Catalog Number	Finish	Thread Size 1 (TS1)	Thread Size 2 (TS2)	Thread Length (TL)	Depth (D)	Height (H)
LPC436LG	Bare	5/8" UNC	1/2" UNC	1 1/2"	1"	6"
LPC436SH	Bare	5/8" UNC	1/2" UNC	7/8"	1"	6"
LPLC436SH	Lead Covered	5/8" UNC	1/2" UNC	7/8"	1"	6"
LPLC436LG	Lead Covered	5/8" UNC	1/2" UNC	1 1/2"	1"	6"

Table 2/2


Catalog Number	Width (W)	Unit Weight
----------------	-----------	-------------

LPC436LG	3"	1.6 lb
LPC436SH	3"	1.6 lb
LPLC436SH	3"	4.17 lb
LPLC436LG	3"	4.17 lb

ADDITIONAL PRODUCT DETAILS

Where applicable, lead covering thickness is a minimum of 1/16" (1.59 mm) and is not included in the stated dimensions.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE