

Insulated Rail Signal Bondstrand



FEATURES

Highly flexible and resistant to vibration fatigue

Allows mechanical or compressed types of connections as well as nVent ERICO Cadweld welded connections

Insulation manufactured from 600 volt-rated PVC

Two insulation thicknesses available: 4/64" (0.063", 1.6 mm) and 6/64" (0.094", 2.4 mm)

Meets or exceeds recommendations and design criteria described in AREMA® Manual Parts 8.1.20, 8.1.25, 8.1.30, 8.1.32 and 10.3.12

SPECIFICATIONS

Number of Wires: 133

Material: Copper Magnesium;Polyvinylchloride

Table 1/1

Catalog Number	Finish	Conductor Type	Color	Conductor Size	Insulation Thickness	Length
SBS17CINSUL	Bare	AREMA® S-17	Black	5/16" Bondstrand	0.06"	100'
SBS17INSUL	Bare	AREMA® S-17	Black	5/16" Bondstrand	0.06"	1000'
SBS17LINSUL	Bare	AREMA® S-17	Black	5/16" Bondstrand	0.06"	500'
SBS8CINORG	Bare	AREMA® S-8	Orange	3/16" Bondstrand	0.06"	100'

CatalogNumber	Finish	ConductorType	Color	Conductor Size	Insulation Thickness	Length
SBS8CINSUL	Bare	AREMA® S-8	Black	3/16" Bondstrand	0.06"	100'
SBS8INORG	Bare	AREMA® S-8	Orange	3/16" Bondstrand	0.06"	1000'
SBS8INSUL	Bare	AREMA® S-8	Black	3/16" Bondstrand	0.06"	1000'
SBS8LINSORG	Bare	AREMA® S-8	Orange	3/16" Bondstrand	0.06"	500'
SBS8LINSUL	Bare	AREMA® S-8	Black	3/16" Bondstrand	0.06"	500'
SBS8TCINS	Tinned	AREMA® S-8	Black	3/16" Bondstrand	0.06"	100'
SBS8TDINSUL	Tinned	AREMA® S-8	Black	3/16" Bondstrand	0.06"	500'
SBS8TINSUL	Tinned	AREMA® S-8	Black	3/16" Bondstrand	0.06"	1000'
SBS8TCINS664	Tinned	AREMA® S-8	Black	3/16" Bondstrand	0.09"	100'
SBS8TCINSRD	Tinned	AREMA® S-8	Red	3/16" Bondstrand	0.09"	100'
SBS8TINSRD	Tinned	AREMA® S-8	Red	3/16" Bondstrand	0.09"	1000'
SBS8TLINS664	Tinned	AREMA® S-8	Black	3/16" Bondstrand	0.09"	500'
SBS8TLINS664 ORG	Tinned	AREMA® S-8	Orange	3/16" Bondstrand	0.09"	500'

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including cadmium and vinyl chloride, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE