

# Joint Bond Mold Pair Only, Signal



## FEATURES

Pair of replacement molds designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

## SPECIFICATIONS

**Material:** Graphite

Table 1/1

| Catalog Number | Rail Type                       | Bond Terminal Style | Product                     | Conductor Size   | Conductor Outer Diameter, Nominal | Welder Style |
|----------------|---------------------------------|---------------------|-----------------------------|------------------|-----------------------------------|--------------|
| SBM456         | 85 lb to 141 lb T-Rail Sections | 3/4" XS             | Mold and Mold Cleaning Tool | 3/16" Bondstrand | 0.19"                             | T6, T7       |
| SBM456M        | 85 lb to 141 lb T-Rail Sections | 3/4" XS             | Mold only                   | 3/16" Bondstrand | 0.19"                             | T6, T7       |
| SBS5838        | 85 lb to 141 lb T-Rail Sections | 3/4" Tab            | Mold and Mold Cleaning Tool | 3/16" Bondstrand | 0.19"                             | T6, T7       |
| SBS5838M       | 85 lb to 141 lb T-Rail Sections | 3/4" Tab            | Mold only                   | 3/16" Bondstrand | 0.19"                             | T6, T7       |
| SBS5839        | 85 lb to 141 lb T-Rail Sections | 1" Tab              | Mold and Mold Cleaning Tool | 3/16" Bondstrand | 0.19"                             | T6, T7       |

| CatalogNumber | Rail Type                       | Bond Terminal Style | Product                     | Conductor Size   | Conductor OuterDiameter, Nominal | Welder Style |
|---------------|---------------------------------|---------------------|-----------------------------|------------------|----------------------------------|--------------|
| SBS5839M      | 85 lb to 141 lb T-Rail Sections | 1" Tab              | Mold only                   | 3/16" Bondstrand | 0.19"                            | T7           |
| SBS925        | Head-Free Rail                  | Head Free           | Mold and Mold Cleaning Tool | 3/16" Bondstrand | 0.19"                            | T6, T7       |
| SBS925M       | Head-Free Rail                  | Head Free           | Mold only                   | 3/16" Bondstrand | 0.19"                            | T6, T7       |
| SBB492        | Head-Free Rail                  | Head Free           | Mold and Mold Cleaning Tool | 5/16" Bondstrand | 0.31"                            | T6, T7       |
| SBB492M       | Head-Free Rail                  | Head Free           | Mold only                   | 5/16" Bondstrand | 0.31"                            | T6, T7       |
| SBS898        | 85 lb to 141 lb T-Rail Sections | 1" Tab              | Mold and Mold Cleaning Tool | 5/16" Bondstrand | 0.31"                            | T6, T7       |
| SBS898M       | 85 lb to 141 lb T-Rail Sections | 1" Tab              | Mold only                   | 5/16" Bondstrand | 0.31"                            | T6, T7       |
| SBTBT71YM     | 85 lb to 141 lb T-Rail Sections | 1" Tab              | Mold only                   | #1 Concentric    | 0.33"                            | T7           |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including silica, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE