

Lightning Card



FEATURES

Ideal for use on land and offshore wind turbines

Unique serial numbers can associate data to the specific location and installation time

Standard CR80 credit card size with HiCo magnetic strip

SPECIFICATIONS

Table 1/1

Catalog Number	Trip Threshold	Temperature	Height	Width
WTBLC10	6 - 300 kA 10/350 μ s	-22 to 176 °F	2 1/8"	3 3/8"

ADDITIONAL PRODUCT DETAILS

Cards are calibrated to measure current in a 10 mm (0.39") circular conductor. A correction factor may be added for card reading to account for alternative conductor geometries.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE