


nVent ERICO Cadweld Plus Rail Track Connector Bond Kit, Single-Leg



The nVent ERICO Cadweld Plus Rail Track Connector Bond Kit, Single-leg, is intended to be welded to the web of the rail at the neutral axis as a single-leg connection. The kit has all the necessary components to establish a welded bond connection to the web of the rail. This technique guarantees connection reliability and consistent electrical resistance, using nVent ERICO Cadweld Plus welding material. The bond is designed to be welded at the rail profile neutral axis level, where the stress and strain are minimal.

FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Available as bond-only or incorporated in a Bond Kit including all necessary parts to ensure easy handling at jobsite

SPECIFICATIONS

Handle Clamp:	C105B x 2, Sold Separately
Material:	Cadmium Bronze;Copper Alloy
Finish:	Electrogalvanized;Tinned
Bond Terminal Style:	Tab

Table 1/1

Catalog Number	Grinding Wheels Included	Conductor Size	Connector Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SBTBBU4ACWP	No	3/16" Bondstrand	3/16" Bondstrand	4 3/4"	11/16"	3/16"

Catalog Number	Grinding Wheels Included	Conductor Size	Connector Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SBTBBU4ACWP W2	Yes	3/16" Bondstrand	3/16" Bondstrand	4 3/4"	11/16"	3/16"
SBTBCU412CW PW2	Yes	3/16" Bondstrand	3/16" Bondstrand	12 3/4"	11/16"	3/16"


ADDITIONAL PRODUCT DETAILS

Kit includes: (100) bonds, (100) PLUSF80 alloy welding material, (1) replacement mold pair, (1) mold cleaner, and (5) grinding wheels (where applicable).

Kits with grinding wheels include (5) high-performance grain, 4.5" (114 mm) diameter (7/8" arbor), Type 27 depressed center wheels (part number SBG20046) for use with an angle style grinders.

nVent ERICO Cadweld Plus welding material requires electronic control unit for ignition (sold separately).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including cadmium, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE