

nVent ERICO Lay-In Split Bolt



nVent ERICO Lay-in Split Bolt is a high-strength corrosion resistant alloy bolt engineered with a round head design to prevent damage to wires plus includes a captive nut and saddle, allowing for no loose hardware. It is ideal for high-volume installations, providing an easy, time-saving, one-handed installation.

FEATURES

Unique rounded head

One hand installation of conductor onto wire basket tray

Install using common tools

Captive nut and saddle, no loose hardware

Direct burial

SPECIFICATIONS

Table 1/1

Catalog Number	Material	A	Tin Plating	Conductor Size
ELSBRH4	Copper	0.129" - 0.235"	No	#8 Solid - #4 Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE