

nVent ERICO PermaGround Compression Connector, Thin Wall C-Crimp



The nVent ERICO PermaGround Compression Connector, Thin Wall C-Crimp, is a versatile and dependable solution for grounding, bonding, and power applications. This connector is made from high-conductivity copper, ensuring maximum conductivity and low contact resistance. It is suitable for circuits rated at 35KV or less, provided that proper high-voltage spacing and insulation techniques are applied. The connector's bright dip finish not only enhances its appearance but also offers excellent resistance to corrosion and oxidation. It is designed for direct burial, making it a reliable choice for various applications.

CERTIFICATIONS





FEATURES

Marked with wire size, die index, and part number for clear and easy identification

Range-taking capability reduces stocking inventory and offers application versatility

Suitable for use in circuits rated 35KV or less with proper high voltage spacing and insulation techniques

Bright dip finish for enhanced appearance and corrosion resistance

SPECIFICATIONS


Table 1/2							
Catalog Number	Material	Conductor Type	Main/Run Conductor Range	Tap Conductor Range	Connection Type	Number of Crimps	
TWCTR10T16	Copper	Solid, Stranded	14 - 10 AWG	16 - 14 AWG	Crimp	1	
TWCTR8T12	Copper	Solid, Stranded	10 - 8 AWG	12 - 10 AWG	Crimp	1	

CatalogNumber	Material	ConductorType	Main/Run Conductor Range	Tap Conductor Range	Connection Type	Number of Crimps
TWCTR6T12	Copper	Solid, Stranded	8 - 6 AWG	12 - 8 AWG	Crimp	1
TWCTR4T12	Copper	Solid, Stranded	6 - 4 AWG	12 - 6 AWG	Crimp	1
TWCTR3T12	Copper	Solid, Stranded	5 - 3 AWG	12 - 6 AWG	Crimp	1
TWCTR2T12	Copper	Solid, Stranded	4 - 2 AWG	12 - 4 AWG	Crimp	1
TWCTR1T12	Copper	Solid, Stranded	3 - 1 AWG	12 - 3 AWG	Crimp	1
TWCTR1/0T12	Copper	Solid, Stranded	2 - 1/0 AWG	12 - 2 AWG	Crimp	1
TWCTR2/0T12	Copper	Solid, Stranded	1 - 2/0 AWG	12 - 1 AWG	Crimp	1
TWCTR3/0T12	Copper	Solid, Stranded	1/0 - 3/0 AWG	12 - 1/0 AWG	Crimp	1

Table 2/2							
Catalog Number	Die Index	Length (L)	Width (W)	Height (H)	Unit Weight	Direct Burial	
TWCTR10T16	W21	0.42"	0.293"	0.361"	0.004 lb	Yes	
TWCTR8T12	W24	0.62"	0.354"	0.459"	0.008 lb	Yes	
TWCTR6T12	W29	0.62"	0.445"	0.554"	0.011 lb	Yes	
TWCTR4T12	W33	1.21"	0.501"	0.617"	0.027 lb	Yes	
TWCTR3T12	W37	1.206"	0.573"	0.721"	0.037 lb	Yes	
TWCTR2T12	W42	1.21"	0.648"	0.798"	0.045 lb	Yes	
TWCTR1T12	W45	1.75"	0.659"	0.822"	0.068 lb	Yes	
TWCTR1/0T12	W50	1.75"	0.755"	0.948"	0.085 lb	Yes	

CatalogNumber	Die Index	Length (L)	Width (W)	Height (H)	Unit Weight	Direct Burial
TWCTR2/0T12	W54	1.75"	0.789"	0.982"	0.089 lb	Yes
TWCTR3/0T12	W62	1.75"	0.886"	1.102"	0.104 lb	Yes

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE