

# nVent ERICO PermaGround Water and Gas Pipe Ground Clamp



nVent ERICO PermaGround Water and Gas Pipe Ground Clamp is engineered of high-strength 6061-T6 aluminum alloy and are used for connecting copper or aluminum conductors to copper water pipe, galvanized pipe or steel conduit. The conductor and pipe range taking capabilities make this connector ideal for installations requiring long ground wire runs.

## **CERTIFICATIONS**







## **FEATURES**

Used for connecting copper water pipe, galvanized pipe or steel conduit

Suitable for use with copper or aluminum conductors

#### **SPECIFICATIONS**

Table 1/1										
Catalog Number	Material	For Outdoor Use	Pipe Size, Nominal (Ø)	Hex Width (W)	Conductor Size	Certifications				
CWP1J	Silicon Bronze	No	1/2" - 1"	1.00" - 1 1/4"	#10 Solid - #2 Solid, 6 mm <sup>2</sup> Solid - 25 mm <sup>2</sup> Stranded	CSA, UL, cUL				
SGC-1/0	Aluminum	No	0.5 - 1		#14 Stranded - 1/0 Stranded	UL KDER				
AGC-1	Aluminum	Yes	0.5 - 1		#14 Stranded - 1/0 Stranded	UL KDER				


CatalogNumber	Material	For OutdoorUse	Pipe Size, Nominal (Ø)	Hex Width (W)	Conductor Size	Certifications
CWP1JSH	Silicon Bronze	Yes	1/2" - 1"	1.00" - 1 1/4"	#10 Solid - #2 Stranded, 6 mm² Stranded - 25 mm² Stranded	cUL, UL
AGC-2	Aluminum	Yes	1.25 - 2		#6 Solid - 250 kcmil Stranded	UL KDER
CWP2JSH	Silicon Bronze	Yes	1 1/4" - 2"	1 1/2" - 2 1/8"	#10 Solid - #2 Stranded, 6 mm² Solid - 25 mm² Stranded	UL, cUL
CWP2J	Silicon Bronze	No	1 1/4" - 2"	1 1/2" - 2 1/8"	#10 Solid - #2 Stranded, 6 mm² Stranded - 25 mm² Stranded	cUL, CSA, UL
CWP3JSH	Silicon Bronze	Yes	2 1/2" - 4"	2 1/2" - 3 1/8"	#10 Solid - #4 Stranded, 6 mm² Stranded - 16 mm² Stranded	cUL, UL
CWP3J	Silicon Bronze	No	2 1/2" - 4"	2 1/2" - 3 1/8"	#10 Solid - #4 Stranded, 6 mm² Stranded - 16 mm² Stranded	UL, cUL
AGC-4	Aluminum	Yes	2.5 - 4		#6 Solid - 250 kcmil Stranded	UL KDER

## **DIAGRAMS**



## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause



<sup>△</sup> WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

# North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE