

nVent ERICO Railclips, Hammer-On, Conductor Parallel Outside



FEATURES

"Hammer-on" design

Securely holds conductors, reducing maintenance and improving wayside safety

Quick and easy hammer-on installation

Fits various rail profiles

Does not require removal of the ballast material

Multi-layer proprietary coating provides optimal corrosion protection


SPECIFICATIONS

Rail Type: 40 kg to 65 kg T-Rail Sections

Finish: Multi-Layer Proprietary Coating; Cataphoresis and Polyester Black Treatment

Material: Spring Steel

Table 1/1				
Catalog Number	Length (L)	Width (W)	Rail Foot Thickness (RFT)	Diameter (Ø)
EM58SN4SH	2.56"	1 3/4"	0.310" - 0.55"	0.530" - 0.61"
EM58SN3SH	2.76"	1 3/4"	0.310" - 0.55"	0.980" - 1.1"



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France: +33 800 901 793 Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE