

Prefabricated Fence Clamp Assembly with Single Ground Lead



FEATURES

Ideal for when nVent ERICO Cadweld connections cannot be made to aluminum pipe or thin-wall steel tube

Stainless steel hardware included

Available in either left or right-hand orientation

SPECIFICATIONS

Material: Copper;Stainless Steel 18-8 (EN 1.4305);Stainless Steel 304 (EN 1.4301)

Finish: Tinned

Table 1/1

Catalog Number	Orientation	Fence Post Size, Nominal	Fence Post Outside Diameter, Actual (Ø)	Ground Lead Conductor Size	Ground Lead Length
A235C2C1LH	Left Hand	1 1/2"	1.9"	1/0 Stranded	1'
A235D2G2RH	Right Hand	2"	2.38"	2/0 Stranded	2'
A235E2Q2RH	Right Hand	2 1/2"	2.88"	4/0 Stranded	2'
A235F2C2LH	Left Hand	3"	3.5"	1/0 Stranded	2'


Catalog Number	Orientation	Fence Post Size, Nominal	Fence Post Outside Diameter, Actual (Ø)	Ground Lead Conductor Size	Ground Lead Length
A235G2Q2RH	Right Hand	3 1/2"	4"	4/0 Stranded	2'
A235H2C10RH	Right Hand	4"	4.5"	1/0 Stranded	10'
A235D2G4LH	Left Hand	2"	2.38"	2/0 Stranded	4'
A235D2Q4RH	Right Hand	2"	2.38"	4/0 Stranded	4'
A235E2G4LH	Left Hand	2 1/2"	2.88"	2/0 Stranded	4'
A235E2Q4LH	Left Hand	2 1/2"	2.88"	4/0 Stranded	4'
A235D2Q4LH	Left Hand	2"	2.38"	4/0 Stranded	4'
A235D2Q5LH	Left Hand	2"	2.38"	4/0 Stranded	5'
A235D2Q5RH	Right Hand	2"	2.38"	4/0 Stranded	5'
A235E2Q5LH	Left Hand	2 1/2"	2.88"	4/0 Stranded	5'
A235E2Q5RH	Right Hand	2 1/2"	2.88"	4/0 Stranded	5'

ADDITIONAL PRODUCT DETAILS

Right hand orientation shown in diagram.

A235-D-2G-2-RH		
A235	Series	
D	Pipe Size	B = 1 1/4" C = 1 1/2" D = 2" E = 2 1/2" F = 3" G = 3-1/2" H = 4"
2G	Ground Lead Cable Code (AWG)	2C = 1/0 Stranded 2G = 2/0 Stranded 2Q = 4/0 Stranded
2	Ground Lead Length (feet)	
RH	Ground Lead Side	LH = Left Hand RH = Right Hand

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE