

Rail Profile Template



FEATURES

Provides specific, safe and easy positioning of hole height on the rail profile

Universal rail profile templates can accommodate multiple rail profiles

Suitable for use with nVent ERICO SBMV2, SBMV4, SBME48VDC and SBME230VAC rail drill machines

Installs easily on rail drill machines

SPECIFICATIONS

Hole Size (HS): 1/4"

Diameter (Ø): 2.13"

Material: Steel

Table 1/1

Catalog Number	Template Type	Width (W)	Rail Type	Hole Height (HH)
RPT100LB	Regular	3 1/4"	100 lb ARAB	2.63"
RPT115LB	Regular	3 1/4"	115 lb AREA	2.98"
RPT132RE	Regular	3 1/4"	132 lb RE	3.2"
RPT136RE	Regular	3 1/4"	136 lb RE, TR68	3.36"
RPT141AB	Regular	3 1/4"	141 lb AB	3.47"

Catalog Number	Template Type	Width (W)	Rail Type	Hole Height (HH)
RPT43KG625	Regular	3 1/4"	43 kg	2.46"
RPT50KG63	Regular	3 1/4"	50 kg	2.48"
RPT60KG738	Regular	3 1/4"	60 kg	2.9"
RPT70LBASCS	Regular	3 1/4"	70 lb ASCS	2.05"
RPT90LB655	Regular	3 1/4"	90 lb ARA, TR45	2.58"
RPT90LBARAA	Regular	3 1/4"	90 lb ARAA	2.54"
RPTAS41KG603	Regular	3 1/4"	AS41	2.37"
RPTAS4758	Regular	3 1/4"	AS47	2.28"
RPTAS47619	Regular	3 1/4"	AS47	2.44"
RPTAS50KG67	Regular	3 1/4"	AS50	2.64"
RPTAS5364	Regular	3 1/4"	AS53	2.52"
RPTAS53AS60NAX	Regular	3 1/4"	AS46, AS53	2.46"
RPTAS6068	Regular	3 1/4"	AS60	2.68"
RPTAS60KG745	Regular	3 1/4"	AS60	2.93"
RPTBH95RBS64	Regular	3 1/4"	BH95RBS	2.55"
RPTBHP42KG58	Regular	3 1/4"	BHP42	2.28"
RPTBS100A	Regular	3 1/4"	BS100A	3"
RPTBS80A	Regular	3 1/4"	BS80A	2.58"

Catalog Number	Template Type	Width (W)	Rail Type	Hole Height (HH)
RPTBS90A56	Regular	3 1/4"	BS90A	2.2"
RPTB50T675	Regular	3 1/4"	50 kg	2.66"
RPTIR52KG69	Regular	3 1/4"	52 kg	2.72"
RPTK4063	Regular	3 1/4"	K40	2.48"
RPTNP4AM805	Regular	3 1/4"	NP4AM	3.17"
RPTNP4AM865	Regular	3 1/4"	NP4AM	3.41"
RPTNP4AM893	Regular	3 1/4"	NP4AM	3.66"
RPTR65785	Regular	3 1/4"	R65	3.09"
RPTRI6087	Regular	3 1/4"	RI60	3.43"
RPTRP42	Regular	3 1/4"	RP42	2.38"
RPTRP54	Regular	3 1/4"	RP54	2.76"
RPTS41595	Regular	3 1/4"	S41	2.34"
RPTS49475	Regular	3 1/4"	S49	1.87"
RPTUIC5472	Regular	3 1/4"	UIC	2.83"
RPTUIC6074	Regular	3 1/4"	UIC60	2.91"
RPTUIC60763	Regular	3 1/4"	UIC60	3"
RPTUNI	Universal	3 3/4"	S49, S54, UIC60	2.46"
RPTUNIVABC	Universal	3 3/4"	BS90A, UIC54, UIC60	2.76"

Catalog Number	Template Type	Width (W)	Rail Type	Hole Height (HH)
RPTUNIVEFG	Universal	3 3/4"	AS50, AS60, BHP42	2.93"
RPTVRC50CN	Regular	3 1/4"	VRC50	2.7"
RPTVRC60CN	Regular	3 1/4"	VRC60	3.11"

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE