

Rail Switch Bond Kit, Signal, Tab Style



FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Highly durable

SPECIFICATIONS

Finish:	Bare;Tinned
Material:	Cadmium Bronze;Copper
Bond Terminal Style:	Tab

Table 1/1


Catalog Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SBTBS3436	3/16" Bondstrand	36"	1"	3/16"
SBTBS3330	3/16" Bondstrand	30"	0.78"	3/16"
SBTBS3324	3/16" Bondstrand	24"	0.78"	3/16"
SBTBS3312	3/16" Bondstrand	12"	0.78"	3/16"

Catalog Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SBTBS3412	3/16" Bondstrand	12"	1"	3/16"
SBTBS3424	3/16" Bondstrand	24"	1"	3/16"
SBTBS3318	3/16" Bondstrand	18"	0.78"	3/16"

ADDITIONAL PRODUCT DETAILS

Kits include: (25) bonds and (50) F80 alloy welding material.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including cadmium, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America	Europe	Europe	APAC
+1.800.753.9221	Netherlands:	Germany:	Shanghai:
Option 1 – Customer Care	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
Option 2 – Technical	France:	Other Countries:	Sydney:
Support	+33 800 901 793	+31 13 5835404	+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE