

Rebar Grounding Clamp, Perpendicular



CERTIFICATIONS



FEATURES

Universal use for rebar, rods or pipes

Lay-in feature cuts installation time

Bronze alloy construction with Stainless Steel 304 screws

Approved for direct burial in earth and concrete

SPECIFICATIONS


Table 1/2

Catalog Number	Material	Connection Type	Conductor Size	Ground Rod Diameter, Actual (Ø)	Water Pipe Size (Ø)	Rebar Size, US
EK17	Bronze, Stainless Steel 304 (EN 1.4301)	Perpendicular	#10 Solid - #2 Solid, 5.5 mm ² Stranded - 25 mm ² Stranded	0.5" - 1"	1/2" - 1"	#4 - #8

Table 2/2

Catalog Number	Rebar Size, Canada
----------------	--------------------

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE