

CABS Hardware Kit, UL®



CERTIFICATIONS



FEATURES

Kit includes 4 threaded rods, 4 inserts, 2 screws, 10 nuts, 6 spacers and sleeve

Multiple rod lengths available to accommodate various busbar widths and profile configurations

Threaded rods are made from non-magnetic stainless steel to reduce the magnetic loop between phases

Insulator sleeves allow for minimal space between phases

Robust hardware provides strength and rigidity

Installs quickly and easily

Time-savings and lower total install costs compared to traditional methods

Engineered and standardized design

RoHS compliant

SPECIFICATIONS

Finish: Electrogalvanized

Material: Stainless Steel 316 (EN 1.4401);Steel;Polyolefin

Table 1/1

Catalog Number	Article Number	Rod Length	Thread Size	Unit Weight
----------------	----------------	------------	-------------	-------------

CABS140HWT	549526	5.51"	M10	0.6 lb
CABS220HWT	549528	8.66"	M10	0.67 lb
CABS190HWT	549527	7.48"	M10	0.66 lb

ADDITIONAL PRODUCT DETAILS

Threaded rods must be installed on both sides of each phase.

Busbar Width	Single Profile Support	Double Profile Support
2"	CABS140HWT	CABS140HWT
2 1/2"		CABS190HWT
3"		
4"	CABS190HWT	
5"	CABS220HWT	
6"		CABS220HWT

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE