

# **CAPB Cap Nut with Threaded Stud**



## **CERTIFICATIONS**



### **FEATURES**

For use with DH Distance Holder and Spacer


## **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel;Polystyrene

**Flammability Rating:** UL® 94HB **Temperature:** 176 °F Max

Table 1/1						
Catalog Number	Article Number	Thread Size (TS)	Thread Length (TL)	Height (H)	Width (W)	Unit Weight
CAP-CAPB6	560850	M6	0.31"	0.47"	0.55"	0.01 lb
CAP-CAPB5	560840	M5	0.31"	0.47"	0.55"	0.01 lb



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

# Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY TRACHTE ERICO HOFFMAN ILSCO SCHROFF**