

# HFBT nVent ERIFLEX Flexibar Bending Tool

## CATALOG NUMBER

**HFBT**



## CERTIFICATIONS



## FEATURES

Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation

Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation

Portable tool can be used on the jobsite or attached to a workbench

Includes tool box

## PRODUCT ATTRIBUTES

Article Number: 558920

Material: Steel

Bending Radius: 0.39"

Bending Angle: 180 ° Max

Depth: 4.72"

Height: 8.46"

Width: 13.58"

Unit Weight: 15.4 lb

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**