

Hydraulic Pump and Foot Controller



CERTIFICATIONS



FEATURES

Directly connects to a single hydraulic tool for operation or can be used as a spare for the Hydraulic nVent ERIFLEX Flexibar and Busbar Work Center

Pump includes hose with quick-release coupler

Foot controller includes two pedals with off, on and safety off positions

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Voltage	Power	Operating Pressure	Oil Flow	Oil Flow
HYDR-PMP-115V	545701	115 V	370W	10000lbf/in ²	0.2l/min	7oz/min

Table 2/2

Catalog Number	Article Number	Tank Capacity	Unit Weight
HYDR-PMP-115V	545701	2 - 4	97 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE