

# **RRCB Round Braid in Coil, Plain Copper**



## **CERTIFICATIONS**



#### **FEATURES**

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

#### **SPECIFICATIONS**

Material: Copper

Table 1/2						
Catalog Number	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
RRCB15-25	557440	150A	49.34kcmil	1416	0.01"	82'
RRCB15-75	557470	300A	148.01kcmil	4236	0.01"	82'
RRCB15-10	557420	75A	19.74kcmil	560	0.01"	82'
RRCB15-30	557450	180A	59.2kcmil	1680	0.01"	82'

CatalogNumber	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
RRCB15-16	557430	120A	31.57kcmil	900	0.01"	82'
RRCB15-50	557460	250A	98.68kcmil	2820	0.01"	82'
RRCB15-6	557400	45A	11.84kcmil	352	0.01"	82'

Table 2/2							
Catalog Number	Article Number	Diameter	Unit Weight				
RRCB15-25	557440	0.31"	0.55 lb				
RRCB15-75	557470	0.55"	1.65 lb				
RRCB15-10	557420	0.2"	0.22 lb				
RRCB15-30	557450	0.35"	0.66 lb				
RRCB15-16	557430	0.24"	0.35 lb				
RRCB15-50	557460	0.43"	1.1 lb				
RRCB15-6	557400	0.16"	0.13 lb				

## **ADDITIONAL PRODUCT DETAILS**

Unit weight is per meter (3.28').

#### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE