

# **TCB Threaded Busbar**



## **CERTIFICATIONS**



### **FEATURES**

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

### **SPECIFICATIONS**

Material: Copper

Table 1/2							
Catalog Number	Article Number	Width (W)	Thickness (T)	Length (L)	Thread Size (TS)	Torque (TQ)	
TCB12X2-1M	549230	0.47"	0.08"	38.98"	M5	0.96 ft·lbf	

CatalogNumber	Article Number	Width (W)	Thickness (T)	Length (L)	Thread Size (TS)	Torque (TQ)
TCB12X4-1M	550200	0.47"	0.16"	38.98"	M5	1.48 ft·lbf
TCB25X4-1M	549210	0.98"	0.16"	39.37"	M6	3.32 ft·lbf
TCB18X4-1M	549200	0.71"	0.16"	39.37"	M8	8.11 ft·lbf
TCB12X4-2M	550190	0.47"	0.16"	78.15"	M5	1.48 ft·lbf
TCB12X5-1M	549220	0.47"	0.2"	38.98"	M5	4.06 ft·lbf

Table 2/2							
Catalog Number	Article Number	A	Unit Weight				
TCB12X2-1M	549230	0.71"	0.66 lb				
TCB12X4-1M	550200	0.71"	0.95 lb				
TCB25X4-1M	549210	0.79"	1.76 lb				
TCB18X4-1M	549200	0.79"	1.32 lb				
TCB12X4-2M	550190	0.71"	1.87 lb				
TCB12X5-1M	549220	0.71"	1.1 lb				

## **DIAGRAMS**

### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE