

APO Cover



APO Covers are designed for use as inspection windows in highly corrosive environments where easy viewing and access is essential.

FEATURES

Covers are maintenance free and corrosion resistant

Included thumb screw inserts allow quick window opening for access to interior component

SPECIFICATIONS

Material: Fiberglass
Color: Light Gray
Color Code: RAL 7035
Finish: Smooth Matte

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Quick Ship
A1-COVERLG	A1-COVERLG	7.32in	5.94in	1.77in	No
A1-CTCOVER	A1-CTCOVER	7.32in	5.94in	1.77in	No
A31-COVERLG	A31-COVERLG	11.89in	7.32in	1.77in	No
A31-CTCOVER	A31-CTCOVER	11.89in	7.32in	1.77in	No
A41-COVERLG	A41-COVERLG	11.89in	11.89in	1.77in	No
A41-CTCOVER	A41-CTCOVER	11.89in	11.89in	1.77in	No
A51-COVERLG	A51-COVERLG	19.2in	11.89in	1.77in	No
A51-CTCOVER	A51-CTCOVER	19.2in	11.89in	1.77in	No
A71-COVERLG	A71-COVERLG	14.65in	11.89in	1.77in	No
A71-CTCOVER	A71-CTCOVER	14.65in	11.89in	1.77in	No
A11-COVERLG	A11-COVERLG	23.74in	14.65in	1.77in	No
A11-CTCOVER	A11-CTCOVER	23.74in	14.65in	1.77in	No
A12-COVERLG	A12-COVERLG	23.74in	23.74in	1.77in	No
A12-CTCOVER	A12-CTCOVER	23.74in	23.74in	1.77in	No
A61-COVERLG	A61-COVERLG	23.74in	11.89in	1.77in	No
A61-CTCOVER	A61-CTCOVER	23.74in	11.89in	1.77in	No

Catalog Number	Article Number	Height	Width	Depth	Quick Ship
A81-COVERLG	A81-COVERLG	21.97in	11.89in	1.77in	No
A81-CTCOVER	A81-CTCOVER	21.97in	11.89in	1.77in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE