

APO Extension Collar



APO Extension Collars support deeper depths of APO enclosures.

FEATURES

Collars are maintenance free and corrosion resistant

Increases APO enclosure depth

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
A1-EXT706LG	A1-EXT706LG	7.32in	5.94in	1.38in	Fiberglass	Smooth Matte
A31-EXT1207LG	A31-EXT1207LG	11.89in	7.32in	1.38in	Fiberglass	Smooth Matte
A41-EXT1212LG	A41-EXT1212LG	11.89in	11.89in	1.38in	Fiberglass	Smooth Matte
A71-EXT1412LG	A71-EXT1412LG	14.65in	11.89in	1.38in	Fiberglass	Smooth Matte
A81-EXT2212LG	A81-EXT2212LG	21.97in	11.89in	2.36in	Fiberglass	Smooth Matte
A61-EXT2412LG	A61-EXT2412LG	23.78in	11.89in	2.36in	Fiberglass	Smooth Matte
A12-EXT2424LG	A12-EXT2424LG	23.74in	23.74in	2.36in	Fiberglass	Smooth Matte
A11-EXT2414LG	A11-EXT2414LG	23.74in	14.65in	2.36in	Fiberglass	Smooth Matte

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE