

APO Front Plate



APO Front Plates allow convenient component mounting toward the front of APO enclosures.

FEATURES

Convenient component mounting toward front of APO enclosures

SPECIFICATIONS

Material: Aluminum

Finish: Mill

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
FP1207A	FP1207A	10.85in	6.28in	0.08in	0.08in	No
FP1212A	FP1212A	10.85in	10.83in	0.08in	0.08in	No
FP1412A	FP1412A	13.57in	10.83in	0.08in	0.08in	No
FP1912A	FP1912A	18.07in	10.83in	0.08in	0.08in	No
FP2212A	FP2212A	20.87in	10.83in	0.08in	0.08in	No
FP2412A	FP2412A	22.57in	10.83in	0.08in	0.08in	No
FP2414A	FP2414A	22.57in	13.55in	0.08in	0.08in	No
FP2424A	FP2424A	22.57in	22.79in	0.08in	0.08in	No
FP706A	FP706A	6.28in	4.89in	0.08in	0.08in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE