


Cable Entry Gland Plate Connected Grommet Small, CCFGS



CCFGS cable glands are used with CCFI, CCFO and CCFR cable entry systems.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12, 4X (indoor only); File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

FEATURES

IP66 Modular Halogen-free and silicone free cable entry system, that provide versatility, variability and variety

Everything mounted from the outside of the enclosure

The frames, inlays and grommets can be combined in many ways - ensuring you many versatile configuration options

The frame does not need to be disassembled if requirements change or carrying out service work

No need to disassemble and reconnect connectors on cables so manufactures warranty is not voided

The conical shape of the grommets allows them to be easily pressed in, provides static strain relief in accordance with DIN EN 62444

For assembly, they are pressed from the inside out into the openings of the assembled inlays

The grommets are available in different sizes to match the diameter of the cable

The CCFGS is first placed around the cable and then inserted into the cable gland

Based on the wave-cut profile, there is no need to remove the connector on the assembled cabled

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
CCFGS15	58352	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS14	58351	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS12	58348	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS13	58349	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS10	58346	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS11	58347	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS8	58344	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS9	58345	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS6	58342	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS7	58343	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS2	58337	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS4	58339	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS5	58341	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS015	58336	0.8in	0.8in	0.7in	Plastic	Untreated
CCFGS3	58338	0.8in	0.8in	0.7in	Plastic	Untreated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE