

## **ComLine OSP Wall-Mount Rack Angles**



The ComLine OSP Wall-Mount Rack Angles are used to mount 19in rack equipment inside the cabinet. They are grounded to the cabinet body through the mounting bolts. Please note the square mounting holes meet EIA standard and each package includes one pair.

## **FEATURES**

The ComLine OSP Wall-Mount Rack Angles are used to mount 19in rack equipment inside the cabinet

They are grounded to the cabinet body through the mounting bolts

Please note the square mounting holes meet EIA standard and each package includes one pair

## **SPECIFICATIONS**

Table 1/1						
Catalog Number	Article Number	Material	Finish	Thickness	Rack Units	Rack Width
ERA19239S	17041	Mild Steel	Zinc Plated	12ga	18U	19in, 23in
ERA196S	17037	Mild Steel	Zinc Plated	12ga	12U	19in
ERA192312S	17042	Mild Steel	Zinc Plated	12ga	25U	19in, 23in
ERA199S	17038	Mild Steel	Zinc Plated	12ga	18U	19in

## **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN TRACHTE ILSCO SCHROFF**