

Concept Panels



Concept panels are taller and wider than corresponding NEMA-size panels.

FEATURES

Painted white or conductive finish

Include a formed flange along any side that is longer than 22.20 in (564 mm)

Optional wood panels are made of 3/4-in plywood, pre-cut and pre-drilled to install on panel mounting studs in the rear of the cabinet

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP2020W	23785	18.2in	18.2in	Plywood	Smooth Matte	
CP3220W	23786	30.2in	18.2in	Plywood	Smooth Matte	
CP4420W	23787	42.2in	18.2in	Plywood	Smooth Matte	
CP1210	29664	10.2in	8.2in	Mild Steel	Powder Coated	White
CP1210G	29665	10.2in	8.2in	Mild Steel	Galvanized	
CP1212	78510	10.2in	10.2in	Mild Steel	Powder Coated	White
CP2020	78550	18.2in	18.2in	Mild Steel	Powder Coated	White
CP2020G	15051	18.2in	18.2in	Mild Steel	Galvanized	
CP2420	78570	22.2in	18.2in	Mild Steel	Powder Coated	White
CP2420G	26469	22.2in	18.2in	Mild Steel	Galvanized	
CP2424	78580	22.2in	22.2in	Mild Steel	Powder Coated	White
CP2424G	26479	22.2in	22.2in	Mild Steel	Galvanized	
CP3024	78610	28.2in	22.2in	Mild Steel	Powder Coated	White
CP3024G	26489	28.2in	22.2in	Mild Steel	Galvanized	
CP3624G	26579	34.2in	22.2in	Mild Steel	Galvanized	
CP3624	78650	34.2in	22.2in	Mild Steel	Powder Coated	White
CP3630	78660	34.2in	28.2in	Mild Steel	Powder Coated	White
CP3630G	26589	34.2in	28.2in	Mild Steel	Galvanized	
CP4230	78680	40.2in	28.2in	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP4230G	15061	40.2in	28.2in	Mild Steel	Galvanized	
CP4236	78690	40.2in	34.2in	Mild Steel	Powder Coated	White
CP4236G	15062	40.2in	34.2in	Mild Steel	Galvanized	
CP4836	78710	46.2in	34.2in	Mild Steel	Powder Coated	White
CP4836G	15064	46.2in	34.2in	Mild Steel	Galvanized	
CP6036G	15065	58.2in	34.2in	Mild Steel	Galvanized	
CP6036	78720	58.2in	34.2in	Mild Steel	Powder Coated	White
CP1212G	26429	10.2in	10.2in	Mild Steel	Galvanized	
CP1612	78520	14.2in	10.2in	Mild Steel	Powder Coated	White
CP1612G	26439	14.2in	10.2in	Mild Steel	Galvanized	
CP1616	78530	14.2in	14.2in	Mild Steel	Powder Coated	White
CP1616G	26449	14.2in	14.2in	Mild Steel	Galvanized	
CP2012	15634	18.2in	10.2in	Mild Steel	Powder Coated	White
CP2012G	15635	18.2in	10.2in	Mild Steel	Galvanized	
CP2014	15633	18.2in	12.2in	Mild Steel	Powder Coated	White
CP2014G	15636	18.2in	12.2in	Mild Steel	Galvanized	
CP2016	78540	18.2in	14.2in	Mild Steel	Powder Coated	White
CP2016G	26459	18.2in	14.2in	Mild Steel	Galvanized	
CP2412	29666	22.2in	10.2in	Mild Steel	Powder Coated	White
CP2412G	29667	22.2in	10.2in	Mild Steel	Galvanized	

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP2416	78560	22.2in	14.2in	Mild Steel	Powder Coated	White
CP2416G	15052	22.2in	14.2in	Mild Steel	Galvanized	
CP2442	78590	22.2in	40.2in	Mild Steel	Powder Coated	White
CP2442G	15053	22.2in	40.2in	Mild Steel	Galvanized	
CP3012	29668	28.2in	10.2in	Mild Steel	Powder Coated	White
CP3012G	29671	28.2in	10.2in	Mild Steel	Galvanized	
CP3016	29672	28.2in	14.2in	Mild Steel	Powder Coated	White
CP3016G	29673	28.2in	14.2in	Mild Steel	Galvanized	
CP3020	78600	28.2in	18.2in	Mild Steel	Powder Coated	White
CP3020G	15054	28.2in	18.2in	Mild Steel	Galvanized	
CP3030	78620	28.2in	28.2in	Mild Steel	Powder Coated	White
CP3030G	15055	28.2in	28.2in	Mild Steel	Galvanized	
CP3048	78630	28.2in	46.2in	Mild Steel	Powder Coated	White
CP3048G	15056	28.2in	46.2in	Mild Steel	Galvanized	
CP3060	78640	28.2in	58.2in	Mild Steel	Powder Coated	White
CP3060G	15057	28.2in	58.2in	Mild Steel	Galvanized	
CP3220	23782	30.2in	18.2in	Mild Steel	Powder Coated	White
CP3636	78670	34.2in	34.2in	Mild Steel	Powder Coated	White
CP3636G	15058	34.2in	34.2in	Mild Steel	Galvanized	
CP4242	29674	40.2in	40.2in	Mild Steel	Powder Coated	White

Catalog Number	Article Number	Height	Width	Material	Finish	Color
CP4242G	29675	40.2in	40.2in	Mild Steel	Galvanized	
CP4260	29676	40.2in	58.2in	Mild Steel	Powder Coated	White
CP4260G	29677	40.2in	58.2in	Mild Steel	Galvanized	
CP4420	23783	42.2in	18.2in	Mild Steel	Powder Coated	White
CP4824	78700	46.2in	22.2in	Mild Steel	Powder Coated	White
CP4824G	15063	46.2in	22.2in	Mild Steel	Galvanized	
CP4848	29678	46.2in	46.2in	Mild Steel	Powder Coated	White
CP4848G	29681	46.2in	46.2in	Mild Steel	Galvanized	
CP5620	23784	53.2in	18.2in	Mild Steel	Powder Coated	White
CP7230G	35272	70.2in	28.2in	Mild Steel	Galvanized	
CP7236	15253	70.2in	34.2in	Mild Steel	Powder Coated	White
CP7230	35271	70.2in	28.2in	Mild Steel	Powder Coated	White

ADDITIONAL PRODUCT DETAILS

Catalog number CP4230 is used on Concept disconnect enclosures.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE