

CS480 Straight Tube



CS480 Straight Tube provides structural integrity and acts as conduit for equipment wiring.

INDUSTRY STANDARDS

IEC 60529, IP66

FEATURES

Wall thickness 3.6-mm

Outer diameter of 48.3-mm

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICATIONS

Finish: Polished
Material: Stainless Steel 304

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
CCSS48T150	42629	59.06in	1.9in	1.9in	0.14in	No
CCSS48T75	42599	29.53in	1.9in	1.9in	0.14in	No
CCSS48T125	42619	49.21in	1.9in	1.9in	0.14in	No
CCSS48T100	42609	39.37in	1.9in	1.9in	0.14in	No
CCSS48T25	42579	9.84in	1.9in	1.9in	0.14in	No
CCSS48T50	42589	19.69in	1.9in	1.9in	0.14in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE