

CS480 U-Shaped Pendant Tube



CS480 U-Shaped Pendant Tube is pre-cut and shaped with two 90-degree bends to reduce assembly time. For use in conjunction with CS480 Stainless Steel Pendant Arm system components.

INDUSTRY STANDARDS

IEC 60529, IP66

FEATURES

Use of these tubes does not compromise the enclosure rating

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFICATIONS

Finish: Polished
Material: Stainless Steel 304

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Thickness	Quick Ship
CCSSTU802480	13713	31.5in	9.45in	31.5in	0.14in	No
CCSSTU502450	13714	19.69in	9.45in	19.69in	0.14in	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE