

Double-Bay Frames



The ProLine frame is the foundational design element that protects the components inside this modular enclosure. The frame was designed to maintain a solid square structure - a solid foundation for the electrical enclosure.

FEATURES

12 gauge (2.5mm), roll-formed steel frame with welded steel corners

Open roll-formed profile design affords complete surface corrosion protection and assembly access

RAL 7035 textured light-gray polyester powder paint finish

Frame features a 25-mm DIN standard, alternating rectangular and round hole pattern

Flange trough collar on door and side openings deflect dust and debris away from the enclosure interior

Welded rear centerpost and cross members to facilitate population in either enclosure bay; no front center post allowing full access for subpanel mounting

Integral frame channels support the full weight of the mounting subpanel (sold separately)

Individual frames designed for joining/baying in multiple directions with the inclusion of joining kits

Provisions for mounting subpanel, rack mounting and grid/rail system mounting to support many unique customer applications; optional center upright to accomplish mounting in individual bays sold separately

Appropriate gasketed door(s) and covers are required to maintain a Type-12 environmental rating, sold separately

SPECIFICATIONS

Thickness: 12ga
Color: Light Gray
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

Catalog Number	Article Number	Material	Max Subpanel Size	Max Rack Mounting Space	Quick Ship
PF12125	29783	Mild Steel	42.72 x 44.49in	24U	No
PF14125	29784	Mild Steel	50.59 x 44.49in	28U	No
PF16125	95530	Mild Steel	58.46 x 44.49in	38U	No
PF16126	95540	Mild Steel	58.46 x 44.49in	33U	No
PF16128	95550	Mild Steel	58.46 x 44.49in	33U	No
PF18124	95700	Mild Steel	66.34 x 44.49in	38U	No
PF18125	95710	Mild Steel	66.34 x 44.49in	38U	No
PF18126	95720	Mild Steel	66.34 x 44.49in	38U	No
PF18128	95730	Mild Steel	66.34 x 44.49in	38U	No
PF18164	29785	Mild Steel	66.34 x 60.24in	38U	No
PF18165	95740	Mild Steel	66.34 x 60.24in	38U	No
PF18166	95750	Mild Steel	66.34 x 60.24in	38U	No
PF18168	95760	Mild Steel	66.34 x 60.24in	38U	No
PF18185	29786	Mild Steel	66.34 x 68.11in	38U	No
PF18186	29787	Mild Steel	66.34 x 68.11in	38U	No
PF20124	95920	Mild Steel	74.21 x 44.49in	42U	No

Catalog Number	Article Number	Material	Max Subpanel Size	Max Rack Mounting Space	Quick Ship
PF20125	95930	Mild Steel	74.21 x 44.49in	42U	No
PF20126	95940	Mild Steel	74.21 x 44.49in	42U	No
PF20128	95950	Mild Steel	74.21 x 44.49in	42U	No
PF20165	95960	Mild Steel	74.21 x 60.24in	42U	No
PF20166	95970	Mild Steel	74.21 x 60.24in	42U	No
PF20168	95980	Mild Steel	74.21 x 60.24in	42U	No
PF20185	25409	Mild Steel	74.21 x 68.11in	42U	No
PF20186	25419	Mild Steel	74.21 x 68.11in	42U	No
PF20188	29788	Mild Steel	74.21 x 68.11in	42U	No
PF22125	96080	Mild Steel	82.09 x 44.49in	47U	No
PF22126	96090	Mild Steel	82.09 x 44.49in	47U	No
PF22128	96100	Mild Steel	82.09 x 44.49in	47U	No
PF7126	95320	Mild Steel	23.03 x 44.49in	13U	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE