

Elbow 45-Degree Feed-Through



Feed-Through 45-Degree Elbows are used for continuous runs with 45-degree turns. Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications.

INDUSTRY STANDARDS

Certified by Canadian Standards Association.

FEATURES

Feed-Through 45-Degree Elbows are used for continuous runs with 45-degree turns

Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications

SPECIFICATIONS

- Color Code:

ANSI 61
- Color:

Gray
- Material:

Mild Steel
- Finish:

Powder Coated

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F22WE45	14080	Elbow	2.5in	2.5in	14ga	No
F88WE45	14690	Elbow	8in	8in	14ga	No
F66WE45	14480	Elbow	6in	6in	14ga	No
F44WE45	14270	Elbow	4in	4in	14ga	No

ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints. Dimension J is from intersection of center lines.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDYERICOHOFFMANILSCOSCHROFFTRACHTE