

Elbow 45-Degree Lay-in Painted



Lay-in Painted 45-Degree Elbows are used for continuous run with 45-degree turns. Top and inside covers removable so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Painted 45-Degree Elbows are used for continuous run with 45-degree turns

Top and inside covers removable so wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Color Code: ANSI 61
Color: Gray
Material: Mild Steel
Finish: Powder Coated

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F22G45E	52080	Elbow	2.5in	2.5in	16ga	No
F1010G45E	45690	Elbow	10in	10in	14ga	No
F1212G45E	51910	Elbow	12in	12in	14ga	No
F33G45E	15487	Elbow	3in	3in	16ga	No
F44G45E	52240	Elbow	4in	4in	16ga	No
F66G45E	52410	Elbow	6in	6in	16ga	No
F88G45E	52670	Elbow	8in	8in	14ga	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE