

Elbow Sweep 90-Degree



Lay-in Galvanized 90-Degree Sweep Elbows are used for large-radius turns. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Galvanized 90-Degree Sweep Elbows are used for large-radius turns

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Color Code: ANSI 61
Color: Gray
Material: Mild Steel
Finish: Powder Coated

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F1010G90SE	45610	Elbow	10in	2.5in	14ga	No
F1212G90SE	51900	Elbow	12in	2.5in	14ga	No
F22G90SE	52570	Elbow	2.5in	2.5in	16ga	No
F44G90SE	52580	Elbow	4in	2.5in	16ga	No
F66G90SE	52590	Elbow	6in	2.5in	16ga	No
F88G90SE	52800	Elbow	8in	2.5in	14ga	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE