

Elbow Sweep 90-Degree Lay-in Galvanized



Lay-in Galvanized 90-Degree Sweep Elbows are used for large-radius turns. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system.

FEATURES

Lay-in Galvanized 90-Degree Sweep Elbows are used for large-radius turns

Lay-in feature allows wires and cables can be laid in along wireway run

No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system

SPECIFICATIONS

Finish: Galvanized
Material: Mild Steel

Table 1/1						
Catalog Number	Article Number	Type	Height	Width	Thickness	Quick Ship
F2290SEGV	88010	Elbow	2.5in	2.5in	16ga	No
F8890SEGV	88790	Elbow	8in	8in	14ga	No
F4490SEGV	88280	Elbow	4in	4in	16ga	No
F6690SEGV	88570	Elbow	6in	6in	16ga	No
F101090SEGV	45680	Elbow	10in	10in	14ga	No
F121290SEGV	88990	Elbow	12in	12in	14ga	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE