

Deep-Hinged Window Kit Type 4 and 4X, 28.19x20.14, SS Type 316

CATALOG NUMBER

AWDH3024N4SS



Deep-Hinged Window Kits provide protection, visibility and easy access to displays, equipment and components installed behind the viewing area. Window kits are conveniently sized to allow direct mounting in the usable door area of any enclosure with a suitably sized mounting surface.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997 (MS)

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997 (MS)

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997 (SS)

cUL Listed per CSA C22.2, No. 94; Type 3R, 4, 4X, 12; File No. E61997 (SS)

Stainless Steel

NEMA/EEMAC Type 3R, 4, 4X, 12

IEC 60529, IP66

Mild Steel

NEMA/EEMAC Type 4, 12

IEC 60529, IP66

CERTIFICATIONS



BABA

FEATURES

Quarter-turn latches for quick access

0.25-in. (6-mm) thick, clear polycarbonate windows for easy viewing

2.5-in. (64-mm) deep to allow for deep controls

Built-in gasket compression stop on back of window kit facilitates flush mounting

Designed for either left or right hinging

Includes mounting template and mounting hardware

Easy-to-remove clip-style hinge pin

Optional Concept handles can be purchased separately to replace the standard quarter-turn latches

PRODUCT ATTRIBUTES

Article Number: 13018

Height: 30in

Width: 24in

Material: Stainless Steel 316L

Finish: Brushed #4

Thickness: 14ga

Window Size: 24.68 x 14.22in

Weight: 24.3lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE