


# Click-In Mounting Profile, CLPK, 74x753x26mm, Zinc Plated, Mild Steel

## CATALOG NUMBER

**CLPK800**



Additional accessories and electrical equipment can be mounted quickly and easily exactly where needed by using these click-in mounting profiles.

## FEATURES

Description: Universal profile for both depth and width fitting on the 25 mm DIN hole pattern of the enclosure's frame or in combination with the CLPF and VB profiles. The 75 mm wide profile is equipped with three rows of holes of which one is turned 90°. This makes it possible to mount the CLPF profiles in both directions. The CLPK can be secured by the use of self tapping screws.

Material: 1.5 mm zinc plated steel.

Pack quantity: 4 profiles.

## PRODUCT ATTRIBUTES

Article Number: CLPK800

Height: 2.91in

Width: 31.5in

Depth: 1.02in

Load Rating: 1600N

Material: Mild Steel

Finish: Zinc Plated

Thickness: 16ga

Package Quantity: 4

Weight: 7.44lb

Enclosure Material: Mild Steel

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**