

Concept HMI Enclosure Black Handle Type 4, 350x450x180mm, Light Gray, Mild Steel

CATALOG NUMBER

CP354518



A traditional landscape-oriented HMI enclosure with handles made of light-gray steel, the Concept HMI Enclosure is unique among HMI enclosure systems when you need a range of customization options. This pendant- or pedestal-mounted system has many possible configurations and modifications, including a removable front plate that makes it easy to install HMI components, an optional door panel can be mounted in the hinged rear door and the ability to accommodate cutouts anywhere on the enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File Number E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997

NEMA Type 4, 12

IEC 60529, IP66

FEATURES

Pre-drilled hole in top for pendant arm mounting

Pedestal mounting when enclosure is inverted

Integral aluminum handle extrusions have a comfort grip that extends the length of the profile; available in black or blue

Hinged rear corner-formed door has a single-point latch, seamless foam-in-place gasket and panel studs

Aluminum removable front plate is .125-in aluminum

Grounding stud on body; bonding provision on door

Simple easy-to-remove and install hinge pins with built-in captive clip

High-torque threadless studs and fasteners on door for mounting optional door panel

PRODUCT ATTRIBUTES

Article Number: 14725

Height (H): 13.78in

Width (W): 17.72in

Weight: 27.9lb

Technical drawing of the 87791732 frame assembly. The drawing includes an isometric view and a top-down view. The isometric view shows the frame with dimensions A, B, C, D, E, M, N, and a central square cutout. The top-down view shows the frame with dimensions 60 mm (2.36 inches) and 60 mm (2.36 inches). The central square cutout has dimensions 60 mm (2.36 inches) and 60 mm (2.36 inches). The frame has a thickness of 60 mm (2.36 inches). The drawing is labeled with the part number 87791732.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE