


Vented Plinth Base Covers, fits 200x1000mm, Black, Steel

CATALOG NUMBER

PPBCV21000



Vented Plinth Base Covers install in the front and rear openings of a standard plinth base in place of Solid Covers. Vented covers allow air to circulate into the enclosure. Vented Plinth Base Covers are available in 100-mm and 200-mm heights. These covers include all necessary mounting hardware. A standard plinth base must be ordered in combination with Vented Plinth Base covers to form a Vented Plinth Base. If using a gland plate with the Vented Plinth Base, order a vented gland plate to provide air circulation through the bottom of the enclosure.

FEATURES

Hardware included

Standard plinth base must be ordered in combination with Vented Plinth Base covers to form a Vented Plinth Base

If a gland plate is needed, opt for a vented gland plate for optimum air flow

PRODUCT ATTRIBUTES

Article Number: 13332

Material: Mild Steel

Frame Type: Single-Bay

Weight: 18lb

Color: Jet Black

Color Code: RAL 9005

Finish: Powder Coated

Thickness: 16ga

ADDITIONAL PRODUCT DETAILS

200 mm Plinth Bases require two sets of covers.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE