

Friction Slide, L



These profiles should be used to support heavy equipment and to relieve forces from the 19" profile brackets.

FEATURES

Description: To support heavy components which are only fitted to the front. Mounted between two 19" profiles. Version fixed with 2 screws per profile, and version with click-in fixation.

Material: Click-in version 1.5 mm and mounted version 3 mm zinc plated steel.

Pack quantity: 1 pair with fixing material.

SPECIFICATIONS

Thickness: 11ga
Material: Mild Steel
Finish: Plated

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Max Load	Enclosure Material
L597	L597	1.69in	23.5in	1.65in	220lb	Mild Steel
L406	L406	1.69in	16in	1.65in	220lb	Mild Steel
L406C	L406C	1.69in	16in	1.65in	110lb	Mild Steel
L470	L470	1.69in	18.5in	1.65in	220lb	Mild Steel
L470C	L470C	1.69in	18.5in	1.65in	110lb	Mild Steel
L700	L700	1.69in	27.56in	1.65in	220lb	Mild Steel
L279	L279	1.69in	11in	1.65in	220lb	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE