

Front/Rear Plinths, P



This plinth allows for cabling without any restrictions. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

FEATURES

Description: Four corner pieces with removable front covers. The side panels PA must be ordered separately. Available heights: 100 and 200 mm. Machining is required.

Material: 2.5 mm mild steel for corner pieces and 1.5 mm mild steel for covers.

Finish: RAL 7022 structured powder coating.

Pack quantity: 4 corner pieces and 2 front covers, with mounting accessories.

SPECIFICATIONS

Thickness: 16ga
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7022
Color: Umbra Gray

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Compatible Enclosure Width	Enclosure Material
P1080	P1080	3.94in	31.22in	3.74in	31.5in	Mild Steel
P2080	P2080	7.87in	31.22in	3.74in	31.5in	Mild Steel
P1120	P1120	3.94in	46.97in	3.74in	47.24in	Mild Steel
P2120	P2120	7.87in	46.97in	3.74in	47.24in	Mild Steel
P1100	P1100	3.94in	39.09in	3.74in	39.37in	Mild Steel
P2100	P2100	7.87in	39.09in	3.74in	39.37in	Mild Steel
P1060	P1060	3.94in	23.35in	3.74in	23.62in	Mild Steel
P2060	P2060	7.87in	23.35in	3.74in	23.62in	Mild Steel
P1040	P1040	3.94in	15.47in	3.74in	15.75in	Mild Steel
P2040	P2040	7.87in	15.47in	3.74in	15.75in	Mild Steel
P1050	P1050	3.94in	19.41in	3.74in	19.69in	Mild Steel
P2050	P2050	7.87in	19.41in	3.74in	19.69in	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE