

Front/Rear Plinths, PF



The front and rear plinth allows for cabling without any restrictions in accordance with the VDE 0113 standard. Installing cables is made easy as the plinth creates extra space underneath the enclosure.

FEATURES

Description: Front and rear plinth sections. For cabling without any restrictions and in accordance with the VDE 0113 standard. The plinth consists of four corner pieces with removable front covers. The side panels PS are to be ordered separately. Produced in 100 mm and 200 mm heights. 200 mm high plinths are delivered with a rear cover for cabling that consists of two removable panels 100 mm high. The front cover is a one piece panel of 200 mm high. All panels have double returns on each side for added strength.

Material: Corner pieces in 2 mm and panels in 1.5 mm mild steel.

Finish: RAL 7022 structured powder coating.

Pack quantity: 1 set of 4 corner pieces including covers. Front and rear panel (2 rear panels for 200 mm high plinths) with mounting accessories. Mounting accessories for side panels PS or transversal profiles PCP.

Mounting requirements: Add the side panels PS for a complete plinth. When combining enclosures it is recommended to add transversal panels PCP for cable duct support and extra rigidity.

SPECIFICATIONS

Thickness: 16ga Material: Mild Steel Finish: Powder Coated RAL 7022 **Color Code:**

Color: Umbra Gray

| Table 1/1 | | | | | | | | | | |
|----------------|----------------|--------|---------|--------|-----------------------|----------------|--|--|--|--|
| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Product Family | | | | |
| PF1080 | PF1080 | 3.94in | 31.5in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2080 | PF2080 | 7.87in | 31.5in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1100 | PF1100 | 3.94in | 39.37in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2100 | PF2100 | 7.87in | 39.37in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1120 | PF1120 | 3.94in | 47.24in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2120 | PF2120 | 7.87in | 47.24in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1040 | PF1040 | 3.94in | 15.75in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2040 | PF2040 | 7.87in | 15.75in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1050 | PF1050 | 3.94in | 19.69in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2050 | PF2050 | 7.87in | 19.69in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1060 | PF1060 | 3.94in | 23.62in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2060 | PF2060 | 7.87in | 23.62in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1070 | PF1070 | 3.94in | 23.54in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF1140 | PF1140 | 3.94in | 15.67in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2070 | PF2070 | 7.87in | 31.42in | 2.46in | Mild Steel | Free-Standing | | | | |
| PF2140 | PF2140 | 7.87in | 55.04in | 2.46in | Mild Steel | Free-Standing | | | | |

| Catalog Number | Article Number | Height | Width | Depth | EnclosureMaterial | Product Family |
|----------------|----------------|--------|---------|--------|-------------------|----------------|
| PF1090 | PF1090 | 3.94in | 35.43in | 2.46in | Mild Steel | Free-Standing |
| PF2090 | PF2090 | 7.87in | 35.43in | 2.46in | Mild Steel | Free-Standing |

ADDITIONAL PRODUCT DETAILS

For enclosures 1600 mm wide use 2 x 800 mm wide plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY HOFFMAN TRACHTE ERICO ILSCO SCHROFF