

# Gland plate with knockouts, AFK



The required number of holes for cable entries can be easily knocked out of this steel gland plate to allow for the cabling required.

## FEATURES

Description: Gland plates with knock-outs according to table.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Thickness:** 18ga  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Knockout Pattern	Gland Plate Type
AFK11R5	AFK11R5	9.53in	5.04in	0.11in	(4) M16, (5) M20, (2) M25, (2) M32	1
AFK11SR5	AFK11SR5	9.53in	3.46in	0.11in	(4) M16, (3) M20	1S
AFK21R5	AFK21R5	13.46in	5.04in	0.11in	(9) M16, (5) M20, (4) M25, (2) M32	2
AFK21SR5	AFK21SR5	13.46in	3.46in	0.11in	(6) M16, (3) M20, (1) M25	2S
AFK31R5	AFK31R5	17.4in	5.04in	0.11in	(18) M16, (5) M20, (4) M25, (2) M32	3
AFK31SR5	AFK31SR5	17.4in	3.46in	0.11in	(9) M16, (4) M20, (1) M25	3S
AFK41R5	AFK41R5	21.34in	5.04in	0.11in	(27) M16, (5) M20, (4) M25, (2) M32	4
AFK42R5	AFK42R5	21.34in	3.46in	0.11in	(18) M16, (14) M20, (3) M25, (1) M32	4
AFK12R5	AFK12R5	9.53in	5.04in	0.12in	(12) M16, (1) M25, (1) M32	1
AFK22R5	AFK22R5	13.46in	5.04in	0.12in	(21) M16, (1) M32, (1) M25	2
AFK32R5	AFK32R5	17.4in	5.04in	0.12in	(21) M16, (10) M20	3

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**