

Glazed Doors, ADCS



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: To replace the standard door, provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s)

Material: 1.5 mm AISI 304 stainless steel, 2 mm for enclosures with a height or width of 600 mm or greater and 4 mm clear safety glass

Finish: 400 pre-grained stainless steel

Protection: Complies with IP55, TYPE 12, 13, IK 07.

Pack quantity: 1 door

The glazed door allows the electrical components to be seen while the enclosure's door is closed

The user can monitor the status of the components without the need for opening the enclosure's door maintaining the ingress protection

SPECIFICATIONS

Thickness: 0.06in
Finish: Brushed
Material: Stainless Steel 304

Table 1/1

Catalog Number	Height	Width	Latch Quantity	Window Size	Enclosure Material	Product Family
ADCS03624	14.17in	9.45in	1	8.62 x 3.27in	Mild Steel	Wall Mounted
ADCS04030	15.75in	11.81in	1	10.2 x 5.63in	Mild Steel	Wall Mounted
ADCS04040	15.75in	15.75in	1	10.2 x 9.57in	Mild Steel	Wall Mounted
ADCS04060	15.75in	23.62in	1	10.2 x 17.44in	Mild Steel	Wall Mounted
ADCS05040	19.69in	15.75in	1	14.13 x 9.57in	Mild Steel	Wall Mounted
ADCS05050	19.69in	19.69in	1	14.13 x 13.5in	Mild Steel	Wall Mounted
ADCS06040	23.62in	15.75in	2	18.07 x 9.57in	Mild Steel	Wall Mounted
ADCS06060	23.62in	23.62in	2	18.07 x 17.44in	Mild Steel	Wall Mounted
ADCS06080	23.62in	31.5in	2	18.07 x 25.31in	Mild Steel	Wall Mounted
ADCS08060	31.5in	23.62in	2	25.94 x 17.44in	Mild Steel	Wall Mounted
ADCS08080	31.5in	31.5in	2	25.94 x 25.31in	Mild Steel	Wall Mounted
ADCS10080	39.37in	31.5in	1	33.82 x 25.31in	Mild Steel	Wall Mounted
ADCS12080	47.24in	31.5in	1	41.69 x 25.31in	Mild Steel	Wall Mounted
ADCS14080	55.12in	31.5in	1	49.57 x 25.31in	Mild Steel	Wall Mounted

ADDITIONAL PRODUCT DETAILS

* 3 point espagnolette locking. Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE