

Glazed Doors, DNG



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

FEATURES

Description: Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

Material: Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55, TYPE 12, IK 07.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMK01 if no door was fitted previously.

SPECIFICATIONS

Thickness: 14ga
Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Window Size | Enclosure Material |
|----------------|----------------|---------|---------|--------|-----------------|--------------------|
| DNG1106R5 | DNG1106R5 | 42.6in | 23.35in | 0.66in | 34.49 x 16.34in | Mild Steel |
| DNG1206R5 | DNG1206R5 | 46.53in | 23.35in | 0.66in | 38.42 x 16.34in | Mild Steel |
| DNG1208R5 | DNG1208R5 | 46.54in | 31.22in | 0.66in | 38.43 x 24.21in | Mild Steel |
| DNG1406R5 | DNG1406R5 | 54.41in | 23.35in | 0.66in | 46.3 x 16.34in | Mild Steel |
| DNG1408R5 | DNG1408R5 | 54.41in | 31.22in | 0.66in | 46.3 x 24.21in | Mild Steel |
| DNG1606R5 | DNG1606R5 | 62.28in | 23.35in | 0.66in | 54.17 x 16.34in | Mild Steel |
| DNG1608R5 | DNG1608R5 | 62.28in | 31.22in | 0.66in | 54.17 x 24.21in | Mild Steel |
| DNG1806R5 | DNG1806R5 | 70.16in | 23.35in | 0.66in | 62.05 x 16.34in | Mild Steel |
| DNG1808R5 | DNG1808R5 | 70.16in | 31.22in | 0.66in | 62.05 x 24.21in | Mild Steel |
| DNG2006R5 | DNG2006R5 | 78.03in | 23.35in | 0.66in | 69.92 x 16.34in | Mild Steel |
| DNG2008R5 | DNG2008R5 | 78.03in | 31.22in | 0.66in | 69.92 x 24.21in | Mild Steel |
| DNG2206R5 | DNG2206R5 | 85.91in | 23.35in | 0.66in | 77.8 x 16.34in | Mild Steel |
| DNG2208R5 | DNG2208R5 | 85.91in | 31.22in | 0.66in | 77.8 x 24.21in | Mild Steel |
| DNG2210R5 | DNG2210R5 | 85.91in | 39.09in | 0.66in | 77.8 x 32.1in | Mild Steel |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE