

Hangers



Hangers are used to support a wireway run. The drop hanger is normally attached to an overhead beam or ceiling while the bracket hanger can be used for wall, floor or ceiling installations. Hangers are finished with paint over plated surfaces.

FEATURES

Hangers are used to support a wireway run

The drop hanger is normally attached to an overhead beam or ceiling while the bracket hanger can be used for wall, floor or ceiling installations

Hangers are finished with paint over plated surfaces

SPECIFICATIONS

Color Code: ANSI 61
Finish: Galvanized; Powder Coated
Color: Gray
Material: Mild Steel

Table 1/1

Catalog Number	Article Number	Type	Height	Width	Thickness	Sealing Plate Type
F22HD	14170	Hanger	2.5in	2.5in	14ga	None
F44HD	14380	Hanger	4in	4in	14ga	None
F66HD	14590	Hanger	6in	6in	14ga	None
F88HD	14990	Hanger	8in	8in	14ga	None
F22HB	14180	Hanger	2.5in	2.5in	14ga	
F44HB	14390	Hanger	4in	4in	14ga	
F66HB	14600	Hanger	6in	6in	14ga	
F88HB	15000	Hanger	8in	8in	14ga	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE